

METAL SOLUTIONS

# EOS CaseHardeningSteel 20MnCr5

## Material Data Sheet

### EOS CASEHARDENINGSTEEL 20MNCR5

Case hardening steel with good hardenability reaching good wear resistance due to high surface hardness after heat treatment.

### MAIN CHARACTERISTICS

- Good wear resistance
- Excellent surface hardness after carburizing
- Material according to EN-10084 alloy number 1.7147
- Carburizable to achieve surface hardness of 60 HRC

**Download Process Data Sheet (PDF)** →

### TYPICAL APPLICATIONS

- Automotive and general engineering applications
- Gears, mechanical parts


## The EOS Quality Triangle

EOS uses an approach that is unique in the AM industry, taking each of the three central technical elements of the production process into account: the system, the material and the process. The data resulting from each combination is assigned a Technology Readiness Level (TRL) which makes the expected performance and production capability of the solution transparent.

EOS incorporates these TRLs into the following two categories:

- Premium products (TRL 7-9): offer highly validated data, proven capability and reproducible part properties.
- Core products (TRL 3 and 5): enable early customer access to newest technology still under development and are therefore less mature with less data.

All of the data stated in this material data sheet is produced according to EOS Quality Management System and international standards



# POWDER PROPERTIES

EOS CaseHardeningSteel 20MnCr5 powder material is in accordance with EN-10084 alloy number 1.7147.

## Powder Chemical Composition (wt.-%)

Element	Min.	Max.
Fe		Balance
Mn	1.1	1.4
Cr	1	1.3
C	0.17	0.22
Si	-	0.4
S	-	0.035

## Powder Particle Size

GENERIC PARTICLE SIZE DISTRIBUTION

15 - 55  $\mu\text{m}$

# HEAT TREATMENT

## Steps

Step 1

Hardening:

840 - 870 °C, hold time 30 min when thoroughly heated, water or oil quenching

Step 2

Tempering:

160 - 200 °C, hold time 2 h when thoroughly heated, air cooling

Optional softening:

Step 1: Hardening


Step 2: Tempering

Optional softening treatment:

Normalizing 870 °C, hold time 1 h when thoroughly heated, air cooling

Optional carburizing in carbon rich atmosphere:

Carburizing treatment 860-900 °C, cooling in air. Hardening and tempering to be performed after carburizing.



## HEADQUARTERS

**EOS GmbH**  
**Electro Optical Systems**

Robert-Stirling-Ring 1  
82152 Krailling / Munich  
Germany

Tel.: +49 89 893 36-0  
Email: [info@eos.info](mailto:info@eos.info)  
URL: [www.eos.info](http://www.eos.info)

---

This powder has not been developed, tested or certified as a medical device according to Directive 93/42/EEC (MDD) or Regulation (EU) 2017/745 (MDR) and is not intended to be used as a medical device, in particular for the purposes specified in Art. 2 No. 1 MDR. Insofar as you intend to use the powder as raw material for the manufacture of pharmaceutical products or medical devices (e.g. as raw material which as a material must meet the requirements of Annex 1, Chapter II MDR), the responsibility and liability for all analyses, tests, evaluations, procedures, risk assessments, conformity assessments, approval and certification procedures as well as for all other official and regulatory measures required for this purpose shall lie solely with you both with regard to the pharmaceutical product and/or medical device manufactured by you and with regard to the properties, suitability, testing, evaluation, risk assessment, other requirements for use of the powder as raw material. In this respect, the limitations of liability pursuant to our General Terms and Conditions and the system sales or material contracts shall apply.

**Part properties are provided for information purposes only and EOS makes no representation or warranty, and disclaims any liability, with respect to actual part properties achieved.** Part properties are dependent on a variety of influencing factors and therefore, actual part properties achieved by the user may deviate from the information stated herein. This document does not on its own represent a sufficient basis for any part design, neither does it provide any agreement or guarantee about the specific properties of a material or part or the suitability of a material or a part for a specific application.

**The achievement of certain part properties as well as the assessment of the suitability of this material for a specific purpose is the sole responsibility of the user. Any information given herein is subject to change without notice.**

---

Status as of 02.12.2024. Subject to technical modifications. EOS is certified according to ISO 9001.

EOS®, Additive Minds®, Alumide®, AMQ®, CarbonMide®, DirectMetal®, DMLS®, EOSAME®, EOSINT®, EOSIZE®, EOSPACE®, EOSPRINT®, EOSTATE®, EOSTYLE®, FORMIGA®, LaserProFusion®, PA 2200®, PrimeCast® and PrimePart® are registered trademarks of EOS GmbH Electro Optical Systems in some countries. For more information visit [www.eos.info/trademarks](http://www.eos.info/trademarks).